

https://www.elecom.co.jp/global/


MAINTENANCE FREE PC

which diagnoses itself




Unexpected Troubles are GONE!

Typical Controller PC




You will know computer troubles, when a factory line stops.

MAINTENANCE FREE PC



You can repair computers, before something happens.

Self-Diagnosis System



Specifications

Model number	LIB-JT15	LIB-JT17	LIG-JB17C	LIG-JB17S	
Display	15 inch	17 inch	N/A		
Resolution	1024 x 768	1280 x 1024	N/A		
Touch	P-Cap 10 points *With Gloves Operation		N/A		
OS	Windows® 10 loT Enterprise 2019 LTSC 64bit		Windows® 10 loT Enterprise 2016 LTSB 64bit		
CPU		Intel® Core™ i5-6300U	i5-6300U (2Core, 2.4GHz, Skylake-U)		
Memory	1x SO-DIMM (DDR4-2133, 4/8/16GB)				
Storage	1x 2.5" SSD (60/120/240GB)		1x mSATA SSD (60/120/240GB)		
LAN	2x RJ45(10/100/1000 Mbps)				
I/F	4x USB 3.0, 2X RS232				
I/F Expansion	1x Expansion Slot (80pins)				
Mounting	VESA: 75 x 75/	VESA: 75 x 75/ 100 x 100 (mm)		Mounting stays are attached.	
VIDEO PORT	N/A		1x VGA		
Speakers	2x 0.6W (Stereo)		N/A		
Dust & Water Resistant	IP65(Front) / IP41(Rear)		IP40		
Vibration / Impact Resistant	2G / 20G		3G / 50G		
Operating Temperature	-10 to 50°C		-20 to 60°C		
Operating Humidity	0 to 90% *Non-Condensing		0 to 90% *Non-Condensing		
Storage Temperature	-20 to 60°C		-25 to 65°C		
Storage Humidity	0 to 90% *Non-Condensing		0 to 90% *Non-Condensing		
Power Input	AC 100 to 240V (60W, 50/60Hz)				
Dimension (mm)	350.5 x 274.5 x 67.5	392.7 x 325.3 x 74.2	260 x 137 x 39.9		
Weight	4.2 Kg	5.2 Kg	2.0 Kg		
Self-Diagnosis function	Client	Client	Client	Client/ Server	

Additional I/F

*Can choose either one.













2x RS232

3x RS232

2x RS232 + 1x USB2.0

2x RS232+1x LAN


4x USB3.0


HDMI + 5.1ch Audio

Appendix

Predictable Components







YAGIWARA Solutions

Head Office

8th Floor, Pacific Square Nagoya Nishiki, 2-5-12 Chuo Ward, Nagoya City, Aichi Prefecture 460-0003

TEL. +81-52-223-1301 FAX. +81-52-223-1303

Osaka

8th Floor, Meiji Yasuda Seimei Osaka Midosuji Building, 4-1-1 Fushimi-machi, Chuo Ward, Osaka City, Osaka Prefecture 541-8765 TEL. +81-6-6223-5011 FAX. +81-6-6223-5012

Tokyo Branch

2F. Kudan First Place. 4-1-28, Kudankita, Chiyoda-ku, Tokyo, Prefecture 102-0073

TEL. +81-3-3556-5016 FAX. +81-3-3556-5018

Fukunka

4th Floor, Higashihie Square Building, 3-12-16 Higashihie, Hakata Ward, Fukuoka City, Fukuoka Prefecture 812-0007 TEL. +81-92-477-8207 FAX. +81-92-477-8208

Look at our website for the latest information on our services.

https://www.hagisol.com